


HT1800 allows to **instantly heat** the solution of water and chemical used for cleaning, for a better cleaning result, even on very dirty carpet or textiles.

The unit is connected to a specific electrical socket on the machine, so that the machine body is powered by one cable only.





Advantages of HT1800

- Santoemma instant heating system allows to get hot water immediately after switching the machine on. It is not necessary to wait a long time before the whole solution tank gets warm, as it happens with many "standard" machines on the market.
- 2. Its modular design allows an easy connection to the machines.
- 3. The boiler has a double protection to avoid overheating. It is also protected against dry working. The status of the 2 thermal protection is shown by 2 lights.
- 4. It is possible to achieve higher temperatures by letting the water re-circulating into the solution tank for some minutes.

Technical Data:

Voltage:	230V - 120V - 100V
Power:	1800W (1500W at 100V)
Cable length:	40 cm for 220V, 15m for 120V and 100V
Dimensions:	11 x 16 x 34 cm.
Weight:	6,5 Kg.

TEMPERATURE INCREASE (Delta T) WITH RESPECT TO THE INPUT TEMPERATURE Water temperature increases when using nozzles with smaller sections

Water-flow	Delta T continuous flow	Delta T working with brief intervals without spraying (max. 20-25 sec.)	
		50% on 50% off	75% on 25% off
0,71 l/min (1 nozzle x 0.1)	~ +35 °C	~ +46 °C	MAX
1,18 l/min (1 nozzle x 0.2)	~ +21 °C	~ +28 °C	~ +42 °C
1,5 l/min (3 nozzles x 0.1)	~ +16 °C	~ +21°C	~ +32 °C
1,87 l/min (1 nozzles x 0.3)	~ +13 °C	~ +17 °C	~ +26 °C
2,19 l/min (5 nozzles x 0.1)	~ +11 °C	~ +14 °C	~ +22 °C
3,33 l/min (3 nozzles x 0.2)	~ +7,5 °C	~ +10 °C	~ +15 °C

With re-circulation of water it is possible to pre-heat the water in the solution tank. In about 10 minutes it is possible to pre-heat 25 litres of water for 10°C. The thermal protections, however, prevent the heating of water over 70° C.

Instant hot water unit, 1800W, complete with metal brackets to fix the heater on the machines.

Machines that can be used with HT1800-220-M:

SABRINA-MAXI – SERENA-SILENT – GRACE-SILENT – CHARIS-ONE - CHARIS-DUAL – ELITE-SILENT – POWERFUL-SILENT

